

BOM list  
for  
Repeater control  
P6Q-400

Art	Type	antal	Bemærkninger	Placering
Modstand	560 ohm	2		R1, R2
Modstand	180 ohm	2		R3, R4
Modstand	6,8 kohm	1		R5
Modstand	18 kohm	1		R7
Modstand	1 kohm	2		R8, R9
Trimme pot.	2,2 kohm	1	Multitune trimmer	R6
Keramisk condensator	470 nf	1		C6
Keramisk condensator	68 nf	1		C7
Elektrolyt kondensator	10uF/16V	4		C1, C2, C3, C4
Elektrolyt kondensator	47uF/16V	1		C5
IC	4066	1		IC1
Optokobler	PC847	1		IC2
IC	LM567	1		IC3